








Image	Configuration	Description of Goods	Seats	S SUNDAY FABRIC	T QUANTA FABRIC	Y FRIDAY FABRIC
 <p>3 SEATER WITH ELE MOTION & TELESCOPIC HEADREST (2CUSH)</p>	CET	** 3 SEATER WITH ELE MOTION WITH ELE TELESCOPIC HEADREST	3			
	<i>w x d x h</i> <i>Seat Width</i>	227x95x88-100 88.5				
 <p>1.5LAF-ELE WITH TELESCOPIC HEADREST</p>	EGT	** 1.5LAF-ELE WITH ELE TELESCOPIC HEADREST	2			
	<i>w x d x h</i> <i>Seat Width</i>	113.5x95x88-100 88.5				
 <p>1.5RAF-ELE WITH TELESCOPIC HEADREST</p>	EHT	** 1.5RAF-ELE WITH ELE TELESCOPIC HEADREST	2			
	<i>w x d x h</i> <i>Seat Width</i>	113.5x95x88-100 88.5				
 <p>1.5NA</p>	EH	1.5 SEAT ARMLESS CHAIR	2			
	<i>w x d x h</i> <i>Seat Width</i>	88.5x95x88-100 88.5				
 <p>1.5NA-ERI(HR-ET) w ELE TELESCOPIC HEADREST</p>	EET	** 1.5S ARMLESS MOT-ELEC WITH ELE TELESCOPIC HEADREST	2			
	<i>w x d x h</i> <i>Seat Width</i>	88.5x95x88-100 88.5				
 <p>2.5RR-EI(HR-ET) WITH TELESCOPIC HEADREST</p>	4ET	** 2.5 SEATER WITH ELE MOTION WITH ELE TELESCOPIC HEADREST	3			
	<i>w x d x h</i> <i>Seat Width</i>	200x95x88-100 75				
 <p>2.5RR-EI(HR-ET) w TELESCOPIC HEADREST & CONSOLE</p>	4ETCS	** 2.5 SEATER WITH ELE MOTION WITH ELE TELESCOPIC HEADREST & CONSOLE	3			
	<i>w x d x h</i> <i>Seat Width</i>	233x95x88-100 75				
 <p>CONSOLE</p>	CS	CONSOLE IN LOUNGE	1			
	<i>w x d x h</i>	33x89x51				
 <p>1.25LAF-ELE w ELE TELESCOPIC HEADREST</p>	ERET	** 1.25LAF-ELE WITH ELE TELESCOPIC HEADREST	1			
	<i>w x d x h</i> <i>Seat Width</i>	100x95x88-100 75				
 <p>1.25RAF-ELE w ELE TELESCOPIC HEADREST</p>	ERRT	** 1.25RAF-ELE WITH ELE TELESCOPIC HEADREST	1			
	<i>w x d x h</i> <i>Seat Width</i>	100x95x88-100 75				
 <p>1.25NA</p>	EQ	1.25 SEAT ARMLESS CHAIR	1			
	<i>w x d x h</i> <i>Seat Width</i>	75x95x88-100 75				
 <p>1.25 NA-ER w TELESCOPIC HEAD</p>	EQT	** 1.25S ARMLESS MOT-ELEC WITH ELE TELESCOPIC HEADREST	1			
	<i>w x d x h</i> <i>Seat Width</i>	75x95x88-100 75				

Please Note: Dimensions quoted on this document are in Centimetres and approximate, may vary slightly from the actual product
All diagrams on the sheet are only provided as an approximate representation of the footprint of the lounge and are in no way intended to represent the actual shape of the lounge.
** Electric recliners require mains power

Image	Configuration	Description of Goods	Seats	S SUNDAY FABRIC	T QUANTA FABRIC	Y FRIDAY FABRIC
 <p>ELECTRIC 2S (2MOT) & TELESCOPIC HEADREST</p>	QET	** 2 SEATER WITH ELE MOTION WITH ELE TELESCOPIC HEADREST	2			
	<i>w x d x h</i> Seat Width	176x95x88-100 63				
 <p>1RAF-ELE w ELE TELESCOPIC HEADREST</p>	ECT	** 1RAF-ELE WITH ELE TELESCOPIC HEADREST	1			
	<i>w x d x h</i> Seat Width	88x95x88-100 63				
 <p>1LAF-ELE w ELE TELESCOPIC HEADREST</p>	EDT	** 1LAF-ELE WITH ELE TELESCOPIC HEADREST	1			
	<i>w x d x h</i> Seat Width	88x95x88-100 63				
 <p>TNA</p>	E	ARMLESS CHAIR	1			
	<i>w x d x h</i> Seat Width	63x95x88-100 63				
 <p>1 NA-ER w TELESCOPIC HEAD</p>	EMT	** 1S ARMLESS MOT-ELEC WITH ELE TELESCOPIC HEADREST	1			
	<i>w x d x h</i> Seat Width	63x95x88-100 63				
 <p>OTTO w STORAGE</p>	DST	STORAGE OTTOMAN	1			
	<i>w x d x h</i>	62x62x43				
 <p>ELEC-RC & TELESCOPIC HEADREST</p>	ERT	** ELECTRIC RECLINER WITH ELE TELESCOPIC HEADREST	1			
	<i>w x d x h</i> Seat Width	123x95x88-100 75				

Please Note: Dimensions quoted on this document are in Centimetres and approximate, may vary slightly from the actual product
 All diagrams on the sheet are only provided as an approximate representation of the footprint of the lounge and are in no way intended to represent the actual shape of the lounge.
 ** Electric recliners require mains power

Web Product Data

Telescopic functioning headrests:

Take your relaxation to new heights, with luxurious powered telescopic headrests which have a vertical rise mechanism - a movement that lifts upwards and tilts forward. This allows you to have the benefit of fine tuning your position with precise movements with no need for any loose pillow cushion support for your head when fully reclined and headrest tilted forward.

The upwards motion of the headrest means you don't need a lounge style with a higher backrest to get the benefit of the higher head support, as it lowers back to a lower back height when not in use.

Zero-gravity recline mechanism:

The ZERO-GRAVITY recline mechanism achieves a sensation of weightlessness by elevating the legs above the heart.

For those living with fluid retention, oedema, poor blood circulation and joint or back pain, this is the type of recliner we recommend.

Not only this health benefit, there is a difference in comfort and lumbar support when compared to a normal operating recliner mechanism.

Construction

COVER TYPE: FABRIC
 COVER DESCRIPTION:
CAT Y = Friday Fabric
 CAT S = Sunday Fabric
 CAT T = Quanta Fabric
 FRAME: Plywood & LVL
 BACK CUSHION & SUSPENSION: Webbing & Siliconized Polyester Fiber Fill + Feather
 SEAT CUSHION: Foam with Polyester Fiber
 SEAT SUSPENSION: Pocketed Coil Spring & No-sag Spring
 Leg: Timber - Ash

Additional Comments

PLEASE NOTE

The headrest of stationary configurations are fixed.

E - 1 SEAT ARMLESS

EQ - 1.25 SEAT ARMLESS

EH - 1.5 SEAT ARMLESS

